


An Efficient Program for Disinfecting

ELECTROSTATIC SPRAYING 101

It is critical to ensure your team and customers that your space is not only clean, but disinfected. Ecolab offers disinfecting solutions and equipment that help you destroy or irreversibly inactivate bacteria and viruses. Solutions that are paired with Electrostatic Spraying can help your disinfecting procedures become more effective and efficient.

Electrostatic Spraying gives you the ability to rapidly and evenly coat hard surfaces with comprehensive coverage:



HIGH-TOUCH, HARD SURFACES AND AREAS CONDUCTIVE TO ELECTROSTATIC SPRAYING USE:



Public Spaces

- Lobbies
- Fitness Centers
- Pool Areas
- Classrooms
- Offices
- Meeting Rooms
- Employee Areas
- Restrooms



High Touchpoints

- Chairs
- Tables
- Countertops
- Desks
- Door Handles
- Escalator Railings
- Stair Railings



Restrooms

- Door Handles
- Faucets
- Toilets
- Countertops
- Dispensers
- Urinal Handles

An Efficient Program for Disinfecting

Better Visibility:
LED lamp

Increased Durability:
Glass-Filled Housing



Ergonomic Handle
with Lock for
Comfort & Safety

Versatility:
Adjustable
3-in-1 nozzle

Double Charge Technology
for Maximum Coverage

Long-Lasting Battery
(4 Hr. Run Time)

1-Litre Easy-Fill Tank



Professional Cordless Electrostatic Handheld Sprayer

Product Specifications

Model #	VP200ESK (10055603)	Weight (Empty)	1.7 kg
Power	Cordless	Weight (Full)	2.7 kg
Tank Size	1L	Optimum Spray Range	60-90 cm

Accessories

Nozzle Setting 1

Nozzle Shape Full Cone

Particle Size 40 microns

Flow Rate 90 mL/min

Run Time per Tank 11.3 min

Coverage per Tank 260 m²

Tanks per Charge 21.2



10055605
1 L Tank



10055611
Carry Strap



10055593
Extra Battery



10055608
3in1 Nozzle



10055595
Extra Charger



10055607
Nozzle
Wrench

